

EasyClassify

Deep Learning classification library



At a Glance

- Includes functions for classifier training and image classification
- Able to detect defective products or sort products into various classes
- Supports data augmentation, works with as few as one hundred training images per class
- Compatible with CPU and GPU processing
- Includes the free Deep Learning Studio application for dataset creation, training and evaluation
- Only available as part of the Deep Learning Bundle

Benefits

New in Open eVision 24.02

EasyFind : Significant speed increase, without any loss of accuracy.

EasyImage

- New Gabor filtering function to help with texture analysis and edge detection.
- New inverse circle warp function, providing conversion between polar and cartesian coordinates.

Easy: Improved off-screen rendering on all platforms.

Admin: Simplified version upgrade procedure with version numbers removed from filenames.

What Is Deep Learning ?

Neural Networks are computing systems inspired by the biological neural networks that constitute the human brain. Convolutional Neural Networks (CNN) are a class of deep, feed-forward artificial neural networks, most commonly applied to analyzing images.

Deep Learning uses large CNNs to solve complex problems difficult or impossible to solve with so-called conventional computer vision algorithms. Deep Learning algorithms may be easier to use as they typically learn by example. They do not require the user to figure out how to classify or inspect parts. Instead, in an initial training phase, they learn just by being shown many images of the parts to be inspected. After successful training, they can be used to classify parts, or detect and segment defects.

EasyClassify Description

EasyClassify is the classification tool of Deep Learning Bundle.

EasyClassify requires the user to label training images, that is to tell which ones are good and which ones are bad, or which ones belong to which class. After this learning/training process, the EasyClassify library is able to classify images. For any given image, it returns a list of probabilities, showing the likelihood that the image belongs to each of the classes it has been taught. For example, if the process requires setting apart bad parts from good ones, EasyClassify returns whether each part is good or bad, and with what probability.

New in Open eVision 23.12

Import of standard datasets into Deep Learning Studio

- Import of COCO Json dataset for EasyLocate or EasySegment Supervised
- Import of YOLO TXT annotations for EasyLocate
- Import of Pascal VOC XML annotations for EasyLocate

EasySpotDetector (Beta release, contact us for more information)

- A single API and license for the alignment of region of interest, surface defect detection (particles, scratches,...) and classification with a custom trained Deep Learning classifier.
- Realtime processing for inline surface inspection

What is EasyClassify good for?

Deep Learning is generally not suitable for applications requiring precise measurement or gauging. It is also not recommended when some types of errors (such as false negative) are completely unacceptable.

EasyClassify performs better than traditional machine vision when the defects are difficult to specify explicitly, for example, when the classification depends on complex shapes and textures at various scales and positions.

Besides, the "learn by example" paradigm of Deep Learning can also reduce the development time of a computer vision process.

Data Augmentation

Deep Learning works by training a neural network, teaching it how to classify a set of reference images. The performance of the process highly depends on how representative and extensive the set of reference images is. Deep Learning Bundle implements "data augmentation", which creates additional reference images by modifying (for example by shifting, rotating, scaling) existing reference images within programmable limits. This allows Deep Learning Bundle to work with as few as one hundred training images per class.

Why Choose Open eVision's Deep Learning Bundle?

- Deep Learning Bundle has been tailored, parametrized and optimized for analyzing images, particularly for machine vision applications.
- Deep Learning Bundle has a simple API and the user can benefit from the power of deep learning technologies with only a few lines of code.
- Try before you buy: Deep Learning Bundle comes with the free Deep Learning Studio training and evaluation application.

EasyClassify, EasySegment and EasyLocate cannot be purchased separately. They are only available as part of the Deep Learning Bundle.

Download and evaluate Deep Learning Bundle using Deep Learning Studio today, and feel free to call Euresys' support should you have any question.

Deep Learning Studio

Open eVision includes the free Deep Learning Studio application. This application assists the user during the creation of the dataset as well as the training and testing of the deep learning tool. For EasySegment, Deep Learning Studio integrates an annotation tool and can transform prediction into ground truth annotation. It also allows to graphically configure the tool to fit performance requirements. For example, after training, one can choose a tradeoff between a better defect detection rate or a better good detection rate.

Performance

Deep Learning generally requires significant amounts of processing power, especially during the learning phase. Deep Learning Bundle supports standard CPUs and automatically detects Nvidia CUDA-compatible GPUs in the PC. Using a single GPU typically accelerates the learning and the processing phases by a factor of 100.

All Open eVision libraries are available for Windows and Linux

- Microsoft Windows 11, 10, 8.1, 7 for x86-64 (64-bit) processor architecture
- Linux for x86-64 (64-bit) and ARMv8-A (64-bit) processor architectures with a glibc version greater or equal to 2.18

Neo Licensing System

- Neo is the new Licensing System of Euresys. It is reliable, state-of-the-art, and is now available to store Open eVision and eGrabber licenses.
- Neo allows you to choose where to activate your licenses, either on a Neo Dongle or in a Neo Software Container. You buy a license, you decide later.
- Neo Dongles offer a sturdy hardware and provide the flexibility to be transferred from a computer to another.
- Neo Software Containers do not need any dedicated hardware, and instead are linked to the computer on which they have been activated.
- Neo ships with its own, dedicated, Neo License Manager, which comes in two flavours: an intuitive, easy to use, Graphical User Interface and a Command Line Interface that allows for easy automation of Neo licensing procedures.

Deep Learning Bundle Feature Comparison

Developed with the support of the DG06 Technology Development Department

Applications

Machine Vision for the Electronic Manufacturing Industry

- PCB inspection
- Mark inspection
- LED inspection

Machine Vision for the General Manufacturing Industries

- Presence / Absence check
- Surface analysis
- Assembly inspection
- Code quality verification for label printing machines

Machine Vision for the Food Inspection Industry

- Food inspection and sorting

Specifications

Software

Host PC Operating System	<ul style="list-style-type: none">• Open eVision is a set of 64-bit libraries that require an Intel compatible processor with the SSE4 instruction set or an ARMv8-A compatible processor.• Open eVision can be used on the following operating systems:<ul style="list-style-type: none">– Microsoft Windows 11, 10, 8.1, 7 for x86-64 (64-bit) processor architecture– Linux for x86-64 (64-bit) and ARMv8-A (64-bit) processor architectures with a glibc version greater or equal to 2.18• Remote connections<ul style="list-style-type: none">– Remote connections are allowed using remote desktop, TeamViewer or any other similar software.• Virtual machines<ul style="list-style-type: none">– Virtual machines are supported. Microsoft Hyper-V, Oracle VirtualBox and libvirt hypervisors have been successfully tested.– Only the Neo Licensing System is compatible with virtualization.• Minimum requirements:<ul style="list-style-type: none">– 2 GB RAM to run an Open eVision application– 8 GB RAM to compile an Open eVision application– Between 100 MB and 2 GB free hard disk space for libraries, depending on selected options.
APIs	<ul style="list-style-type: none">• Supported Integrated Development Environments and Programming Languages:<ul style="list-style-type: none">– Microsoft Visual Studio 2017 (C++, C#, VB .NET, C++/CLI)– Microsoft Visual Studio 2019 (C++, C#, VB .NET, C++/CLI)– Microsoft Visual Studio 2022 (C++, C#, VB .NET, C++/CLI)– QtCreator 4.15 with Qt 5.12

Ordering Information

Product code - Description	<ul style="list-style-type: none">• 4187 - Open EasyClassify for USB dongle• 4237 - Open EasyClassify for PAR dongle• 4337 - Open eVision EasyClassify
Optional accessories	<ul style="list-style-type: none">• 6512 - eVision/Open eVision USB Dongle (empty)• 6513 - eVision/Open eVision Parallel Dongle (empty)• 6514 - Neo USB Dongle (empty)



EMEA

Euresys SA

Liège Science Park - Rue du Bois Saint-Jean, 20
4102 Seraing - Belgium

Email: sales.europe@euresys.com

EMEA

Sensor to Image GmbH

Lechtorstasse 20
86956 Schongau - Germany

Email: sales.europe@euresys.com

AMERICA

Euresys Inc.

316 Prado Way
Greenville, SC 29607 - United States

Email: sales.americas@euresys.com

ASIA

Euresys Pte. Ltd.

750A Chai Chee Road - #07-15 ESR BizPark @ Chai Chee
Singapore 469001 - Singapore

Email: sales.asia@euresys.com

CHINA

Euresys Shanghai Liaison Office

Unit 802, Tower B, Greenland The Center - No.500 Yunjin Road, Xuhui District
200232 Shanghai - China

Euresys上海联络处

上海市徐汇区云锦路500号绿地汇中心B座802室
200232

Email: sales.china@euresys.com

CHINA

Euresys Shenzhen Liaison Office

Room 1202 - Chinese Overseas Scholars Venture Building
518057 Shenzhen - China

Euresys深圳联络处

深圳南山区留学生创业大厦1期1202
518057

Email: sales.china@euresys.com

JAPAN

Euresys Japan K.K.

Expert Office Shinyokohama - Nisso Dai 18 Building, Shinyokohama 3-7-18, Kohoku
Yokohama 222-0033 - Japan
〒222-0033

神奈川県横浜市港北区新横浜3-7-18 日総第18ビル エキスパートオフィス新横浜

Email: sales.japan@euresys.com

More at www.euresys.com

